

Examination Lights

EXCEPTIONALLY BRIGHT LIGHT FOR EVERYDAY USE

HEINE Examination Lights incorporate the latest in illumination technology: Flexible halogen examination lights with innovative bulb technology for exceptional brightness.

The three different mounting options by wheeled stand, wall- or clamp-mounting provide ideal solutions for the daily practice environment.



HEINE HL 5000® Examination Light

Powerful Universal Halogen Light



✧ Two flexible sections

✧ Exceptionally-high light output

✧ 140,000 Lux at 30 cm

With an exceptionally-high light output of 140,000 lux at a distance of 30 cm the HL 5000 Examination Light is ideal for examining and recognizing small details. The flexible gooseneck construction provides a working radius of 120 cm. Three versions are available: wheeled stand, wall mounting, multi-purpose clamp.

- ✧ **Long-lasting 12V/50W halogen bulb** gives 140,000 Lux light output at 30 cm. Very bright, white light.
- ✧ **Extremely compact illumination head.** No obstruction of view, ease of handling.
- ✧ **3 different mounting options: wall, table or wheeled stand.** Versatile.
- ✧ **Halogen bulb lasts at least 4000 hours.** Economical.
- ✧ **Additional UV filter.** Increased safety during examination.
- ✧ **Solid construction with high-specification 120 cm radius gooseneck design.** Super-wide radius of operation, easy to position, light stays put in any selected position.
- ✧ **Additional IR-Filter reduces heat.** More comfort for the patient and examiner.

HL 5000 Examination Light	12V/50W
on non-tip wheeled stand, metal base [01]	J-005.27.106
on lightweight wheeled stand L, polycarbonat base [02]	J-005.27.108
with wall mount [03]	J-005.27.102
with clamp mount [04]	J-005.27.104
Halogen spare bulb 12V/50W [05]	J-005.27.111



[01]



[02]



[03]



[04]



[05]

HEINE HL 1200® Examination Light



Two flexible sections

Ultra-slim head

90,000 Lux at 30 cm

- **Ultra-slim head.** More freedom of movement and an unobstructed view for the examiner.
- **Built-in temperature filter.** Avoids patient discomfort.
- **Exceeds all relevant quality standards.** Guaranteed protection for the patient even if e. g. a bulb fails.
- **“Stay-put” construction of flexible section.** Adjust the light to virtually any position and it “stays-put”, will not sag or droop.
- **Special non-tip wheeled stand.** Resists tipping to improve safety in clinic and practice.
- **Long-life 12V/20W lamp.** 4000 hours bulb life.
- **90,000Lux light output at 30 cm.** Bright, white light.

HL 1200 Examination Light, 12V/20W	black	white
with wheeled stand, metal base [01]	J-005.27.068	J-005.27.067
with lightweight wheeled stand, polycarbonate base [02]	J-005.27.078	J-005.27.077
with additional multi-purpose clamp [03]	J-005.27.056	J-005.27.058
with wall-mounting bracket, can also be fitted to opt. wheeled stand [04]	J-005.27.052	J-005.27.054
Halogen spare bulb 12V/20W [05]	J-005.27.075	J-005.27.075



Wheeled stand (metal base) with mount for HL 1200 Light	Y-096.50.004
Wheeled stand (polycarbonate base) with mount for HL 1200 Light	Y-096.50.009
Mount for HL 1200 Light for wheeled stand	J-000.27.069



[01]



[02]



[03]



[04]



[05]

HEINE HKL® Universal Fiber Optic (F.O.) Examination Light

The ideal light for any doctor's practice. Provides light similar to daylight. Can be powered by any HEINE F.O. Projector.

- ✦ **Adjustable Diaphragm Aperture.** Wide range of spot sizes. Bright, even light. No temperature increase.
- ✦ **Colour temperature 3800K.** "Daylight" illumination.
- ✦ **Long, flexible arm "stays put" where required.** Very flexible to position with long-reach arm.
- ✦ **Slimline head.** Unobstructed view.
- ✦ **Universal-mounting.** Suits the practitioner's needs.
- ✦ **Can be retro-mounted to existing projectors.** Makes an examination light out of any projector.
- ✦ **30,000 Lux light output at 20 cm with projector HK7000.**
- ✦ **Mounting options:**
 - on wheeled stand [01]
 - with clamp for table-top mounting (maximum 40 mm thick) [02]
 - with clamp for vertical mounting to a tube up to 40 mm dia. [03]
 - with clamp for mounting to square tube up to 40 mm dia. [04]
 - wall-mounting for HK7000 Projector [05]



[01]



[02]



[03]



[04]




[05]

HKL Light	F.O.
on wheeled stand [01]	J-003.27.004
with clamp [02] [03] [04]	J-003.27.001
with wall-bracket [05]	J-003.27.002

Black clamp, only	J-000.27.010
White clamp, only	J-000.27.012
Base plate, only	J-000.27.011
Wheeled stand without base-plate	Y-096.50.001
Wheeled stand with base-plate	Y-096.50.002

Please order the projector separately. See page 160.

Light spot sizes




230V is the standard mains voltage. If a different voltage is required, e. g. 120V, please specify when ordering.

**A company makes history and gives a name to
outstanding product quality: HEINE.**

Founded in 1946, family owned, rich in tradition and today international market leader in a complete range of diagnostic instruments. HEINE products meet all international standards (ISO/CE) and represent the leading edge in precision and ergonomic design. Ongoing dedication to research and development has created a solid and diverse technology base for continued quality and product leadership. Over 500 employees worldwide contribute to this success.

www.heine.com



■ HEINE SUBSIDIARY COMPANIES
■ HEINE REPRESENTATIVES

GERMANY

HEINE Optotechnik GmbH & Co. KG
82211 Herrsching
Kientalstr. 7
Tel. +49 (0) 81 52-38 0
Fax +49 (0) 81 52-3 82 02
E-Mail: info@heine.com

NORTH AMERICA

HEINE USA LTD.
10 Innovation Way
Dover, NH 03820
Tel. (603) 7 42-71 03
Fax (603) 7 42-72 17
Toll Free (800) 367-4872
E-Mail: service@heine-na.com

AUSTRALIA

HEINE AUSTRALIA PTY. LTD.
Unit 9, 98 Old Pittwater Road
P.O. Box 717 Brookvale 2100
New South Wales
Tel. +61 (0) 2-99 38 95 00
Fax +61 (0) 2-99 39 23 05
E-Mail: info@heine.com.au

SWITZERLAND

HEINE (Schweiz) AG
Tobelackerstr. 9
CH-8212 Neuhausen am Rheinfl
Tel. +41 (0) 52-6 72 22 66
Fax +41 (0) 52-6 72 63 77
E-Mail: heine-schweiz@schaffhausen.ch

Your distributor

10/11. A-000.00.100 e

